



Replacement Connector Front Body, 5-Wire 20A 3-Phase 347/600V.

Features & Benefits

All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.

Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.

North American products come completely ready to wire, for quick, simple installation. And all feature chemical-resistant thermoplastic construction.

An exclusive, hinged cord grip eliminates loose parts that get lost.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Industrial	Standard	UL Listed

Dimensions

Product Width US	3.4 in	Product Depth US	6.7 in
Product Height US	3.5 in		

Technical Information

Number of Wires	5	Amperage	20 A
Number of Poles	4-Way	Voltage	347 V