



4-Pole, 5-Wire, Non-Fusible Mechanical Interlock. 30A, 3Y, 277/480V.

## Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

## Specifications

### General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | Gray       |
| Country Of Origin | United States  | Application Sector | Industrial |
| Standard          | UL Listed      |                    |            |

### Technical Information

|          |         |                 |       |
|----------|---------|-----------------|-------|
| Phase    | 3       | Number of Wires | 5     |
| Amperage | 30 A    | Number of Poles | 4-Way |
| Voltage  | 277.0 V |                 |       |