



Replacement Plug Front Body, 5-Wire 30A 3-Phase 277/480V.

Features & Benefits

All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.

North American products come completely ready to wire, for quick, simple installation. And all feature chemical-resistant thermoplastic construction.

Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.

An exclusive, hinged cord grip eliminates loose parts that get lost.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Industrial	Standard	UL Listed
Type	Plug Tail		

Dimensions

Product Width US	3.98 in	Product Depth US	6.7 in
Product Height US	3.98 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	NO	cULus Listed	Yes
---------------------	----	--------------	-----

Technical Information

Number of Wires	5	Amperage	30 A
-----------------	---	----------	------

Number of Poles	4-Way	Voltage	277 V
-----------------	-------	---------	-------