



Pass and Seymour
MaxGrip M3 Connector, Gray
Part No. PS5369GRY

Straight Blade Connector 2-Pole 3-Wire 20A 125V, Gray



Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Enclosed terminals provide solid, internally-clamped connections.

High-visibility yellow and orange, or gray.

For covering patents, see www.legrand.us/patents.

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Molded finger grips promote safe, sure handling.

Hospital Grade version displays the Hospital Grade green dot.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL498		

Dimensions

Product Width US	1.34 in	Product Depth US	1.21 in
Product Height US	1.83 in		

Technical Information

Phase	3	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	18 - 12 AWG	Voltage	125.0 V
