



Pass and Seymour
20A, 250V Extra-Hard Use Hospital-Grade Angled Plug, Black and Clear
Part No. PS5466HGAN



STR BLD ANGLE PLUG 3W 20A 250V HG

Features & Benefits

Angle plugs and adapters both allow for 4-position face rotation.

Tri-drive assembly and cord-grip screws are standard on all angle adapters.

Angle adapter (sold separately as catalog number EHU15AN) will accommodate all Pass & Seymour EHU-style Straight Blade plugs and connectors on a retrofit basis. Simply remove the straight handle body from the plug or connector face assembly, and replace with the angle adapter.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498	Type	Straight Blade

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Wire Size	18 - 10 AWG

Voltage

250.0 V
