



Replacement Plug Front Body, 5-Wire 60A 3-Phase 347/600V.

## Features & Benefits

All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.

North American products come completely ready to wire, for quick, simple installation. And all feature chemical-resistant thermoplastic construction.

Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.

An exclusive, hinged cord grip eliminates loose parts that get lost.

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Industrial	Standard	UL Listed
Type	Plug Tail		

### Dimensions

Product Width US	4.5 in	Product Depth US	10.0 in
Product Height US	4.5 in		

### Technical Information

Number of Wires	5	Amperage	60 A
Number of Poles	4-Way	Voltage	347.0 V