



Pass and Seymour  
Straight Blade CONN 3W 15A 250V HG PS5669XHG  
Part No. PS5669XHG

Straight Blade Connector 2-Pole 3-Wire 15A 250V Hospital Grade



### Features & Benefits

|   |   |
|---|---|
| Unit arrives completely ready-to-wire, cuts installation time significantly.                              | Nylon housing provides impact and chemical resistance.  |
| Rugged two-piece cord grip provides more uniform cord retention.  | Internal dust shield keeps terminals free of contaminants.  |
| Tri-drive assembly screws are standard on Hospital Grade plugs and connectors (angle plugs not included). | All 3-wire terminals located on the same plane, allows for quick wire termination from any angle. |
| Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.             | Cord-grip screws recessed to protect installer against screwdriver head slippage.                 |
| For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .            |   |

### Specifications

#### General Info

|                   |                |                    |                        |
|-------------------|----------------|--------------------|------------------------|
| Product Line      | Pass & Seymour | Color              | Black                  |
| Country Of Origin | Mexico         | Application Sector | Residential/Commercial |
| Standard          | UL498          |                    |                        |

#### Dimensions

|                  |          |                   |          |
|------------------|----------|-------------------|----------|
| Product Width US | 1.358 in | Product Length US | 2.638 in |
|------------------|----------|-------------------|----------|

#### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

---

Additional Information

---

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

---

Technical Information

---

|           |             |                 |             |
|-----------|-------------|-----------------|-------------|
| Phase     | 3           | Number of Wires | 3           |
| Amperage  | 15 A        | Number of Poles | Double Pole |
| Wire Size | 18 - 12 AWG | Voltage         | 250.0 V     |

---