



Pass and Seymour  
20A, 277V Extra-Hard Use Spec-Grade Plug, Black and White  
Part No. PS5866X

20A, 277V Extra-Hard Use Spec-Grade Plug and White



## Features & Benefits

Unit arrives completely ready-to-wire, cuts installation time significantly.

Nylon housing provides impact and chemical resistance.

Rugged two-piece cord grip provides more uniform cord retention.

Internal dust shield keeps terminals free of contaminants.

Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.

All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.

Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.

Cord-grip screws recessed to protect installer against screwdriver head slippage.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498	Type	Straight Blade

### Dimensions

Product Width US	1.516 in	Product Length US	1.752 in
------------------	----------	-------------------	----------

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

---

## Technical Information

---

Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Wire Size	18 - 10 AWG
Voltage	277.0 V		

---