



Pass and Seymour

Discontinued - Heavy Duty Hospital Grade Smooth Face Receptacles, Back and Side Wire, 15A, 125V, Ivory

Part No. PS8200HSI



Heavy-Duty Hospital Grade Smooth Face Duplex Receptacle Back and Side-Wire 15A 125V

## Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Two drive screws anchor strap to back body and face.

Internal screw-pressure-plate back and side wire capability.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Tri-drive brass terminal screws.

Two back wire holes for more wiring flexibility.

Smooth face version features an impact-resistant nylon face for ease of cleaning and less dirt build-up.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42		

### Dimensions

Product Width US	1.322 in	Product Depth US	1.18 in
------------------	----------	------------------	---------

