



Pass and Seymour
Stainless Steel Safety Switch with Auxiliary Contact, 30 Amps
Part No. PSDS30AX



30 Amps Stainless Steel Safety Switch with Auxiliary Contact. Legrand's 316-Grade Stainless Steel Safety Switches are designed to provide superior corrosion resistance in harsh environments like food and beverage processing plants where wash down/hose down at extreme temperatures is a daily necessity, as well as environments where salts, acids, and chemicals are prevalent. Legrand's Stainless Steel Safety Switches with NEMA 4X/12, IP66, 67, and 69K ratings are the best solution for durability and personnel safety in any environment.

Features & Benefits

Type 316 grade stainless steel provides superior resistance to corrosion.

8 conduit entry points for flexible installation options.

Certified by the National Sanitation Foundation (NSF) for hygiene requirements in food & beverage processing.

Can accommodate up to 3 sets of auxiliary contacts for control circuit applications.

3/4" standoffs on mounting feet allow adequate space for runoff and inspection behind the switch.

Water- and dust-tight enclosure rated NEMA 3R, 4, 4X, 12K and IP66, 67, 69 for protection against high-pressure, high-temperature water from multiple directions.

High-visibility yellow and red handle can be padlocked to meet OSHA lockout/tagout requirements.

OSHA-compliant Lockout/Tagout.

Multiple drill points for ease of installation (each side and back).

No labels on cover, stamped-in ON/OFF.

Inability to remove cover when in ON position.

Captive cover screws.

Compact footprint.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
--------------	----------------	-------------------	---------------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Amperage	30 A
----------	------
