



PlugTail® Hospital-Grade Tamper-Resistant 15A Self-Test GFCI Receptacle

## Specifications

### General Info

|                   |                        |                    |                        |
|-------------------|------------------------|--------------------|------------------------|
| Product Line      | Pass & Seymour         | Color              | Light Almond           |
| Country Of Origin | China                  | Application Sector | Residential/Commercial |
| Standard          | cULus, UL Listed, FSUL |                    |                        |

### Dimensions

|                   |         |                  |        |
|-------------------|---------|------------------|--------|
| Product Width US  | 1.72 in | Product Depth US | 1.2 in |
| Product Height US | 4.2 in  |                  |        |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Technical Information

|                          |                        |                  |         |
|--------------------------|------------------------|------------------|---------|
| Is Tamper-Resistant      | Yes                    | Interrupt Rating | 4 A     |
| Frequency Rating         | 60 Hz                  | Trip Range       | 5±1 mA  |
| Connection               | Built-in Connector     | Amperage         | 15 A    |
| Number of Poles          | Double Pole            | Voltage          | 125.0 V |
| Environmental Conditions | 95% Humidity, UL 94 V2 |                  |         |