



Pass and Seymour

PlugTail® Specification Grade Tamper-Resistant 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Gray
Part No. PT2097TRGRY



PlugTail® Spec-Grade Tamper-Resistant 20A Self-Test Duplex GFCI. Self-test GFCI Technology - conducts an automatic test every three seconds, ensuring it's always ready to protect. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Plated steel wrap strap design for maximum durability and corrosion resistance.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	China	Number of Receptacles	2
Outlet Type	GFCI, Indoor, Residential, Tamper-Resistant	Application Sector	Residential/Commercial
Standard	cULus, UL Listed, FSUL	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.72 in	Product Depth US	1.2 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Interrupt Rating	4 A
Frequency Rating	60 Hz	Trip Range	5±1 mA
Connection	Built-in Connector	Number of Gangs	1
Amperage	20 A	Mounting Type	Box

Voltage	125.0 V	Environmental Conditions	95% Humidity, UL 94 V2
---------	---------	--------------------------	------------------------