



Pass and Seymour  
PT 20A 120/277V SP SW BK  
Part No. PT20AC1BK

PlugTail® Single-Pole 20A Toggle Switch

## Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Impact- and chemical- resistant cover.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

One-piece nickel-plated mounting strap for superior corrosion resistance.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Auto-ground clip assures positive ground.

Shallow design for easier installation.

Heavy-duty bumpers for quiet, smooth operation.

No exposed terminals create a finger-safe application before, during, and after installation.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
--------------	----------------	-------	-------

Country Of Origin	Mexico
-------------------	--------

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

Amperage	20 A
----------	------