



Pass and Seymour  
PlugTail® Specification Grade Illuminated 20A Toggle Switch, Ivory  
Part No. PT20AC1ISL



Single-Pole Illuminated Toggle Switch, 20A 120/277V For detailed PlugTail information, visit our PlugTail Headquarters.

## Features & Benefits

One-piece nickel-plated mounting strap for superior corrosion resistance

Large brass contacts snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Glass-reinforced nylon back body for durability and strength.

Shallow design for easier installation.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

No exposed terminals create a finger safe application before, during, and after installation.

Heavy-duty bumpers for quiet, smooth operation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL 20		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

---

## Technical Information

---

Actuator	Toggle	Contact Rating	20amp, 120/277vac
Amperage	20 A	Action	DPDT
Number of Poles	Double Pole	Voltage	120.0 V

---