



These durable, dependable receptacles feature a permanently marked, differentiated solution that meets all necessary code requirements. For detailed PlugTail® information, visit our PlugTail® Headquarters.

Features & Benefits

| | |
|--|---|
| .032 inch thick, brass, triple-wipe power contacts for lasting retention. | Plated steel wrap strap design for maximum durability and corrosion resistance. |
| No exposed terminals create a finger safe application before, during, and after installation. | Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections. |
| Dual mechanical shutter system to help prevent insertion of foreign objects (TR models). | Permanent controlled markings on face of receptacle compliant with ASHRAE 90.1, CA Title 24, and NEC. |
| Auto-ground clip assures positive ground. | Half-controlled versions include welded, pre-wired lead that control top half of receptacle for split circuit applications. |
| For covering patents, see www.legrand.us/patents . | For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here . |

Specifications

General Info

| | | | |
|-------------------|----------------|-------|-------|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | Mexico | | |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
| Product Height US | 2.635 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

Amperage

15 A
