



Pass and Seymour  
PlugTail® Isolated Ground Spec Grade Receptacles, 20A, 125V, Red  
Part No. PTIG5362RED



PlugTail® Isolated Ground Spec Grade Duplex Receptacle 20 A 125 V

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

Plated steel wrap strap design for maximum durability and corrosion resistance.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | Red        |
| Country Of Origin | Mexico         | Application Sector | Commercial |
| Standard          | UL 498         |                    |            |

---

## Dimensions

---

|                   |         |                  |          |
|-------------------|---------|------------------|----------|
| Product Width US  | 1.5 in  | Product Depth US | 0.625 in |
| Product Height US | 2.75 in |                  |          |

---

## Listing Agencies / 3rd Party Agencies

---

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

## Technical Information

---

|           |             |                 |             |
|-----------|-------------|-----------------|-------------|
| Phase     | 3           | Number of Wires | 3           |
| Amperage  | 20 A        | Number of Poles | Double Pole |
| Wire Size | 14 - 10 AWG | Voltage         | 125.0 V     |

---