



Pass and Seymour  
PlugTail® Connector in Orange, Right Angle, Stranded, 6-in XHHW-2 Wire  
Part No. PTR6STROR

PlugTail® Connectors, Right Angle, Stranded, 6-inch PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle. Orange connector makes identifying isolated ground circuits easier.

## Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

Distinguished orange connector head to help identify isolated ground circuits during rough in or device replacement.

PlugTail™ Orange Connector: #12 AWG, THHN, copper conductor, 6 - in leads, stripped, stranded, for use with PlugTail Receptacles only

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Orange	Country Of Origin	Mexico
Construction	Injection molded plastic	Features	Plug-In, Right Angle
Package Quantity	1	Application Sector	Commercial
Standard	RoHS, cULus	Warranty Type	1-Year

### Dimensions

Product Width US	1.0 in	Product Weight US	0.06 lb
Product Height US	1.0 in	Product Length US	6.0 in

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

### Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

### Technical Information

---

Wire Size	12 AWG	Indoor/Outdoor	Indoor
-----------	--------	----------------	--------

---

Connection Type	Plugtail, Wired	Environmental Conditions	0 to 95% (relative humidity, non-condensing)
-----------------	-----------------	--------------------------	--

---