



PlugTail® Connectors, Right Angle with IDEAL connector Stranded, 6-inch PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle. Orange connector makes identifying isolated ground circuits easier.

Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

Distinguished orange connector head to help identify isolated ground circuits during rough in or device replacement. Ideal connectors for fast and secure wire termination.

PlugTail™ Orange Connector: #12 AWG, THHN, copper conductor, 6 - in leads, stripped, stranded, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Orange	Country Of Origin	Mexico
Construction	Injection molded plastic	Features	Plug-In, Right Angle
Package Quantity	1	Application Sector	Commercial
Standard	RoHS, cULus	Warranty Type	1-Year
Type	Accessory		

Dimensions

Product Width US	1.0 in	Product Weight US	0.06 lb
Product Height US	1.0 in	Product Length US	6.0 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Conformant Yes

Technical Information

Wire Size 12 AWG Indoor/Outdoor Indoor

Connection Type Plugtail, Wired Environmental Conditions 0 to 95% (relative humidity, non-condensing)
