



PlugTail® Switch Right Angle Connector 4-Wire, 6-inch Solid THHN12

## Features & Benefits

All PlugTail: Connectors are available in any wire length up to 25 inches

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Audible snapping latch assures connection, allows release.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Large crimped and welded brass contacts

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 20

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Contact Rating	120/277vac	Number of Poles	3-Way
Wattage	3 W	Voltage	120.0 V