



Pass and Seymour
Discontinued - PlugTail® Commercial Passive Infrared (PIR) Wall Switch Sensor, Ivory
 Part No. PTWSP250I



Commercial Occupancy Sensor (PIR) PlugTail Automatic Wall Switch with 3 Wire Technology. Compact decorator design, shallow 1" back body, positive detection indicator with no minimum load requirement. Available in Ivory, White, Gray and Light Almond.

For detailed PlugTail information, visit our [PlugTail Headquarters](#).

Features & Benefits

Detection Signature Analysis provides high immunity to RFI and EMI.

Integrated light level sensor works from 10 to 150 footcandles.

Compatible with all electronic and magnetic ballasts, PL lamp balasts, compact fluorescent.

Adjustable time delay of 30 seconds to 30 minutes.

Dual 120/277VAC operation, Adjustable sensitivity from 20% to 100%, 180 degree coverage of up to 900 sq. ft.

Patented voltage drop protection and zero crossing circuitry.

No exposed terminals create a fingersafe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	WS-301-I
Color	Ivory	Country Of Origin	Mexico
Application Sector	Commercial/Industrial	Standard	CSA Listed, cULus, UL Listed

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Target Size

180 deg

Response Frequency

60 Hz

Sensor Type

Occupancy

Sensing Range

900 sq ft

Sensitivity

60Hz

Load

120/277VAC

Environmental Conditions

Indoor Use Only
