



radiant Collection
radiant® Two Single-Pole Switches and Single Pole/3-Way Switch, White
Part No. RCD113W



More control, less space. This combination switch provides control of multiple lights or devices from a single location, while featuring an oversized primary switch for easy use. Designed to emulate the sleek lines of the collection's paddle switches, it delivers flexible, space-saving control with the sophisticated look of radiant. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Offers installation flexibility with space-saving style, as part of the extensive offering from the radiant® Collection. Features durable, high-impact resistant thermoplastic construction.

Designed to install easily with a narrower back body and captivated mounting screws. Patented Snap-In Light Module (sold separately) transforms a combination switch into an illuminated switch in seconds.

More color options available to fit any style, including finishes to match current hardware and lighting trends. Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

| | | | |
|--------------------|-------------------------|--------------------|----------------------------|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | China | Features | Combination, Locator Light |
| Switch Type | Push | Number of Switches | 3 |
| Application Sector | Residential | Standard | cULus, UL Listed |
| Warranty Type | 1-Year Limited Warranty | Type | Switch |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.29 in | Product Depth US | 1.59 in |
| Product Height US | 3.81 in | | |

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

| | | | |
|--------------------------|---------|------------------|--------------------|
| Contact Configuration | 15A | Operating Cycles | 50000 |
| Contact Rating | 120 | Number of Gangs | 1 |
| Amperage | 15 A | Number of Poles | 3-Way, Single Pole |
| Mounting Type | Box | Voltage | 120.0 V |
| Environmental Conditions | UL94 V2 | | |