




radiant Collection  
radiant® Single Pole/3-Way Switch with 15A Tamper-Resistant Outlet, White  
Part No. RCD38TRW



A step up from ordinary, this combination switch and outlet from the radiant® Collection provides convenience and flexibility, as well as style. Operable in both single-pole and 3-way applications, you can use it alone to control one light or fixture, or use with another 3-Way switch for controlling the light from two locations. Also includes a tamper-resistant outlet for safe access to the basic power every home needs. Part of the radiant® Collection, it features clean lines and a smooth finish for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Replaces a standard switch/outlet with ease, in as little as 10 minutes.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style.

Offers installation flexibility, working in both single-pole and 3-way applications.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Number of Receptacles	1	Features	Combination, Locator Light
Switch Type	Push	Number of Switches	1
Outlet Type	Tamper-Resistant	Application Sector	Residential
Standard	cULus, UL Listed	Warranty Type	1-Year Limited Warranty
Type	Outlet, Switch		

### Dimensions

Product Width US	1.29 in	Product Depth US	1.59 in
Product Height US	3.81 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Is Tamper-Resistant	Yes	Contact Configuration	15A
Operating Cycles	50000	Contact Rating	125
Number of Gangs	1	Amperage	15 A
Number of Poles	Single Pole	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Mounting Type	Box
Voltage	120.0 V	Environmental Conditions	Flammability Rating: UL 94 V2