



Pass and Seymour
4-in Round Ceiling Box
Part No. S120RFAN



Ceiling Fan Box with two captive mounting nails. Standard Grade.
Four Auto/Clamps. 30 pack.

Features & Benefits

- Constructed of impact-resitant Noryl thermoplastic, making it virtually unbreakable and non-conductive.
 - Auto Clamp cable clamps molded in, hold wire securly in box.
 - UL Listed for fan and fixture support.
 - Large, 20.25 cubic inch capacity for extra wiring space.
 - Depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling.
 - Angled, rugged, metal mounting bracket safely and securely fastens fans or fixtures to the building structure.
 - Dual mounting accepts fans or fixtures with 2.75 inch or 3.5 inch straps.
 - Fan mounts directly to bracket through box with #10-32 screws (provided).
 - Phillips-head screws (#10-32 x 3 inch) mount the fan or fixture directly to the metal bracket.
 - Ringed nails for tighter grip.
- For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|--------------|------------------------|-------------------|---------------|
| Product Line | Pass & Seymour | Country Of Origin | United States |
| Standard | Residential/Commercial | | |

Dimensions

| | |
|----------------|-------------|
| Cubic Capacity | 20.25 cu in |
|----------------|-------------|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | |
|-------------------|---|
| Number of Outlets | 1 |
|-------------------|---|
