



**Wiremold**  
**GFCI PLUGMOLD 6FT STAINLESS STEEL 11 OUTLETS AND SELF TEST GFCI MOD**  
 Part No. S20GB606TRGFI6



Plugmold® Multioutlet Systems are available in a wide variety of lengths and fittings and in a variety of finishes to provide versatile solutions for many applications. Plugmold options include single or alternating circuits, standard or isolated ground receptacles, GFCI protection, tamper-resistant protection, USB charging, Snapicoil® harnesses of prewired receptacles, and cord-ended units. Plugmold® Multioutlet Systems are available in black or ivory ScuffCoat™ finish, painted white or gray enamel steel, stylish stainless steel, anodized aluminum and durable textured ivory nonmetallic. The painted steel product works with many types of decor and is paintable to integrate with most color schemes. Durable stainless steel and anodized aluminum Plugmold products are corrosion-resistant, making them ideal for labs.

## Features & Benefits

Compact, low profile appearance. Enhanced aesthetics and ideal for installations within minimal spaces.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776188080
Country Of Origin	United States	Number of Receptacles	1
Application Sector	Residential	Standard	cULus Listed Base & Blank Cover: File e4376 Guide RJBT, Multi-Outlet Assemblies: File E15191 Guide PVGT, Fittings: File E41751 Guide RJPR, Base & Blank Cover: Meets Article 386 of NEC, Plugmold Strips: Meets Article 380 of NEC
Type	Plugmold		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

### Buy American Act Compliance

NAFTA	Yes
-------	-----

---

## Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

## Technical Information

---

Frequency Rating	60 Hz	Amperage	20 A
------------------	-------	----------	------

---

Enclosure Type	Stainless Steel	Voltage	125.0 V
----------------	-----------------	---------	---------

---