



radiant Collection
radiant® 15A Single-Pole Switch, Nickel
Part No. TM870NICC10



The perfect upgrade for your basic light switch, the Single-Pole Switch from the radiant® Collection provides on/off control of a light or fixture from a single location, while combining clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Replaces any standard switch with ease, in as little as 10 minutes

Uses a paddle switch for smoother control with a low-profile aesthetic

Features durable, high-impact resistant thermoplastic construction

Designed to install easily with a narrower back body and captivated mounting screws

More color options available to fit any style, including finishes to match current hardware and lighting trends

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

Specifications

General Info

Product Line	Pass & Seymour	Color	Nickel
Country Of Origin	China	Switch Type	Paddle
Number of Switches	1	Application Sector	Residential
Standard	CSA Listed, UL Listed	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.43 in	Product Depth US	1.27 in
Product Height US	4.19 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Operating Cycles	50000	Contact Rating	120V
------------------	-------	----------------	------

Number of Gangs	1	Amperage	15 A
-----------------	---	----------	------

Number of Poles	Single Pole	Mounting Type	Box
-----------------	-------------	---------------	-----

Voltage	120/277 V	Environmental Conditions	UL94 V2
---------	-----------	--------------------------	---------
