



Pass and Seymour  
**Discontinued - Tamper-Resistant Single Receptacle with 3.1A USB Charger, Black**  
 Part No. TM88USBBKCC6



Charge more devices with less clutter. Legrand's full line of charging solutions is designed to power up mobile devices quickly and reliably without the need for bulky AC adapters.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

## Features & Benefits

- Classic duplex style matches traditional devices like 3232s
- Compatible with USB 2.0 & 3.0 devices
- Side and back-wire terminals
- Self-grounding clip standard on all Commercial and Hospital Grade models
- cULus listed
- 2 USB A-Type charging ports 3.1A total charging capacity (simultaneously charges 2 tablets)
- Efficient 5Vdc transformer
- Tamper-Resistant receptacle to meet latest NEC: code requirements
- Slim 1.3-inch depth

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	China		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Is Tamper-Resistant	Yes	USB Amperage	3.1 A
USB Power Output	15 W	Amperage	15 A