



radiant Collection  
radiant® Spec Grade 20A Tamper Resistant Receptacle, White, 100-Pack  
Part No. TR26352WB100

Commercial Specification Grade Tamper-Resistant Decorator 20A  
125V Duplex Receptacle with Back and Side Wire, NEMA 5-20R, cULus  
Made exclusively for use with screwless Wall Plates from the  
radiant® Collection, sold separately.

## Features & Benefits

Made exclusively for use with screwless Wall Plates from the radiant®  
Collection, sold separately.

Impact-resistant nylon face for durability

.032-inch thick brass triple-wipe power contacts for reliable plug retention

Easily accessed break-off, line-contact  
connecting tab for fast, easy split-circuit  
wiring

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate  
with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Indoor, Tamper-Resistant
Package Quantity	1	Application Sector	Commercial
Standard	UL, cULus	Type	Decorator, Outlet, Tamper-Resistant

### Dimensions

Product Width US	1.37 in	Product Height US	3.91 in
Product Length US	0.93 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	cULus 498 C22.2 No. 42	cULus Listed	Yes
---------------------	------------------------	--------------	-----

### Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

### Technical Information

---

Number of Gangs	1	Amperage	20 A
-----------------	---	----------	------

---

Current Rating	20 A	Indoor/Outdoor	Indoor
----------------	------	----------------	--------

---

Mounting Type	Box	Voltage	125.0 V
---------------	-----	---------	---------

---

Environmental Conditions	95% (relative humidity, non-condensing)
--------------------------	---

---