



Hospital-Grade Tamper-Resistant Compact Design Receptacle, Back and Side Wire, 20A, 125V

Features & Benefits

Impact-resistant nylon face.

Stainless steel mounting screws also resist corrosion.

Easily accessible break-off line contact connecting tab for split circuit wiring.

Corrosion-resistant, zinc-plated steel strap is locked in.

Internal screw-pressure-plate back wire and side wire line terminals accept #14 : #10 AWG copper or copper-clad conductors.

High strength thermoplastic back body.

Compact design for easy installation.

Tri-drive terminal and mounting screws.

Meets National Electrical Code Tamper-Resistant requirements.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Wire Size: #14 - #10 AWG Copper Conductor Only

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor, Tamper-Resistant
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
------------------	----------	------------------	---------

Product Height US	2.635 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Amperage	20 A
---------------------	-----	----------	------

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

Voltage	125.0 V
---------	---------