



Vantage
UNIV DIMMER MODULE 8 LOAD 120V ONLY w/CURRENT SENSING
Part No. UDM08-EM-II



The InFusion Universal Dimming Module (UDM08-EM) provides load agnostic phase control as a component of Vantage's centralized lighting control system. It can be mounted in a main or secondary power enclosure and supports control of up to 8 dimmable, forward and reverse phase type loads with up to four line feeds supporting up to 32 amps of total load per module. The module is designed to automatically detect load type, forward or reverse phase. In addition, with current sensing built in, the UDM supports enhanced conditional programming in Design Center for increased support of energy management scenarios.

Features & Benefits

Supports control of up to 8 forward or reverse phase loads

Each dimming channel can be programmable to match the dimming curve of the lighting load

4 Line feeds supporting up to 32 amps per module, 10 amps maximum output for any of the 8 loads

Overload and fuse protection built-in

Module design eliminates the need for field wiring to the module

Specifications

General Info

Product Line	Vantage	UPC Number	840624140658
Country Of Origin	China		

Dimensions

Product Width US	11.0 in	Product Weight US	5.86 lb
Product Volume US	840.94 cu in	Product Depth US	11.5 in
Product Height US	6.5 in	Product Length US	11.25 in