



Weather-Resistant Tamper-Resistant Heavy Duty Spec Grade Single Receptacle, Back and Side Wire, 20A, 250V

Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly	One-piece brass, triple-wipe power contacts for lasting retention
Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring	Impact-resistant nylon face and thermoplastic back body
Internal screw-pressure-plate back wire capable of accepting 14 to 10 AWG solid or stranded copper or copper-clad wire	Terminal compartments isolated from each other for positive conductor containment
Tri-drive terminal and mounting screws	Auto-ground clip assures positive ground
WR marking on face as required by UL Standard	

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Glossy	Country Of Origin	Mexico
Receptacle Type	Single	Number of Receptacles	1
Outlet Type	Weather-Resistant	Application Sector	Commercial
Standard	UL, CSA	Warranty Type	1-Year Limited Warranty
Type	Outlet, Tamper-Resistant, Weather-Resistant		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	E140596
cULus Listed	Yes	CSA File Number	C22.2 No. 42

Technical Information

Is Tamper-Resistant	Yes	Connection	Back and/or Side Wire
Amperage	20 A	Wire Size	14 - 10 AWG
Is Weather Resistant	Yes	Indoor/Outdoor	Outdoor
Mounting Type	Box	Voltage	250.0 V
Connection Type	Wired	Environmental Conditions	Flammability: UL94 V2