



Vantage
AccentPoint II Relay, White
Part No. BCS_VA_APREL



This plug-in relay connects to Vantage's RadioLink wireless solution and provides 15 combined Amps of control for lamps, motors, pumps, or other devices. Two separate devices can be independently controlled from keypads, timed events, sensors, and more. Two models are available, either a ground-up or ground-down plug orientation.

Features & Benefits

- Communicates with the Vantage system through RadioLink technology
- Enables two separate devices to be independently controlled by commands received from keypads, timed events, sensors, and more
- Provides 15 combined Amps of relay control for lamps, motors, pumps, or other devices
- Two models are available, either a ground-up or ground-down plug orientation.

Specifications

General Info

Product Line	Vantage	Color	White
UPC Number	840624100324	Country Of Origin	China
Works With	InFusion, QLink	Application Sector	Residential
Standard	FCC, UL, cUL	Type	Dual Relay Wall Switch Occupancy/Vacancy Sensor

Dimensions

Product Width US	3.125 in	Product Weight US	5.8 oz
Product Depth US	1.25 in	Product Height US	4.125 in

Listing Agencies / 3rd Party Agencies

FCC Compliant

Yes

cUL Listed

Yes

Technical Information

Operating Temperature Min 32 °F

Operating Temperature Max 95 °F

Amperage 15 A

Bulb Compatibility Incandescent

Indoor/Outdoor Indoor

Lighting Types Incandescent

Supply Voltage 120 V

Operating Temperature 0°-35°C, 32°-95°F

Connection Type Plug-In

Load Type
General purpose AC,
Incandescent,
Magnetic low-voltage,
Motor load, Resistive
load

Environmental Conditions 5 to 95% (relative humidity, non-condensing)
