
Pass and Seymour
15A Single Pole, Double Throw Switch, Red
Part No. 1250RED



Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating.Tested to 3 Amps, 24Vdc rating.

Features & Benefits

- Oversize silver alloy contacts for long life and better heat dissipation.
- Fiber terminal insulation barriers standard.
- Bodies, covers, and toggles molded of durable nylon.
- Locking Switches supplied with one 1498-NT key.
- For covering patents, see www.legrand.us/patents.
- Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.
- Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.
- Single Pole-Double Throw and Double Pole-Double Throw.
- Normally open.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	Mexico	Standard	UL Listed

Dimensions

Product Width US	1.5 in	Product Depth US	1.469 in
Product Height US	3.281 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes

Technical Information

Amperage	15 A	Wattage	1 W
Voltage	120 V		