Pass and Seymour
Stainless Steel Safety Switch, 60As HP
Part No. PSDS60HP



60 Amps HP Stainless Steel Safety Switch.Legrands 316-Grade Stainless Steel Safety Switches are designed to provide superior corrosion resistance in harsh environments like food and beverage processing plants where wash down/hose down at extreme temperatures is a daily necessity, as well as environments where salts, acids, and chemicals are prevalent. Legrands Stainless Steel Safety Switches with NEMA 4X/12, IP66, 67, and 69K ratings are the best solution for durability and personnel safety in any environment.

Features & Benefits

- Type 316 grade stainless steel provides superior resistance to corrosion.
- Certified by the National Sanitation Foundation (NSF) for hygiene requirements in food & beverage processing.
- 3/4'' standoffs on mounting feet allow adequate space for runoff and inspection behind the switch.
- High-visibility yellow and red handle can be padlocked to meet OSHA lockout/tagout requirements.
- Multiple drill points for ease of installation (each side and back).
- Inability to remove cover when in ON position.
- Compact footprint.
- 8 conduit entry points for flexible installation options.
- Can accommodate up to 3 sets of auxiliary contacts for control circuit applications.
- Water- and dust-tight enclosure rated NEMA 3R, 4, 4X,12K and IP66,67,69 for protection against high-pressure, high-temperature water from multiple directions.
- OSHA-compliant Lockout/Tagout.
- No labels on cover, stamped-in ON/OFF.
- Captive cover screws.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States

Dimensions

Product Width US	8.3 in	Product Depth US	7.1 in
Product Height US	14.03 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes

Technical Information

Amperage	60 A