On-Q

4-Way Digital Cable Splitter with Coax Network Support

Part No. VM2204V1



This professional-grade digital cable splitter distributes HDTV Antenna/Digital Cable and coax data network signals to three devices. Ideal for MoCA-capable networks.

Features & Benefits

Mounts in single size module space for Greyfox compatible systems 4 LNB inputs, 1 CATV/ANT input, and 4 outputs (combined satellite and CATV/ ANT)

6kV Surge Protection on all ports

Compatible with existing and future networks such as MoCA, VoIP, and DOCSIS 3.0

Coax networking adapters and splitters are not compatible with satellite television systems

Specifications

General Info

Product Line	On-Q	UPC Number	804428066255
Country Of Origin	China	Application Sector	Residential

Technical Information

Connector	ANSI/SCTE 01 Compliant ECT F-port	Temperature Rating	-40° - 60° C
Return Loss	INPUT, 5-40MHz: 22dB, 41-550MHz: 25dB, 551-1002MHz: 24dB. OUTPUT, 5-14MHz: 25dB, 15-40MHz: 38dB, 41-200MHz: 30dB, 201-550MHz: 25dB, 551-1002MHz: 24dB	Impedance	75 ohms