Pass and Seymour

# 30A Single Pole Double Throw Switch, Brown

Part No. 1227



Single-Pole, Double-Throw Switch, 30A, 120/277V.

## Features & Benefits

| | |
|---|---|
| Oversize silver alloy contacts for long life and better heat dissipation. | Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors. |
| Fiber terminal insulation barriers standard. | Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures. |
| Bodies, covers, and toggles molded of durable nylon. | Single Pole-Double Throw and Double Pole-Double Throw. |
| Locking Switches supplied with one 1498-NT key. | Normally open. |
| For covering patents, see https://www.legrand.us/patents. | For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, visit www.legrand.us/electrical-wiring-devices/wall-plates. |

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Brown |
| Finish | Matte | UPC Number | 785007122701 |
| Country Of Origin | Mexico | Application Sector | Commercial, Residential |
| Standard | UL Listed | Type | Manual Controller |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 1.5 in | Product Depth US | 1.469 in |

| | |
|---|---|
| Product Height US | 3.281 in |

## Listing Agencies / 3rd Party Agencies

| | | | |
|---|---|---|---|
| CSA Listed | Yes | cULus Listed | Yes |
| CSA File Number | 17949 | | |

## Technical Information

| | | | |
|---|---|---|---|
| Throw Type | Double Throw | Amperage | 30 A |
| Number of Poles | Single Pole | Wire Size | #14 - #10 AWG |