Pass and Seymour

Locking 30A Double Pole, Double Throw Switch

Part No. 1256L

Manual Controller, Double-Pole, Double-Throw Manual Control Switch, 30A, 120/277V, Locking.

Features & Benefits

- Oversize silver alloy contacts for long life and better heat dissipation.
- Fiber terminal insulation barriers standard.
- Bodies, covers, and toggles molded of durable nylon.
- Locking Switches supplied with one 1498-NT key.
- For covering patents, see www.legrand.us/patents.
- Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.
- Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.
- Single Pole-Double Throw and Double Pole-Double Throw.
- Normally open.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007410754
Country Of Origin	Mexico	Application Sector	Commercial, Residential
Standard	UL Listed	Type	Manual Controller

Dimensions

Product Width US	1.5 in	Product Depth US	1.469 in
Product Height US	3.281 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
CSA File Number	17949		

Technical Information

Amperage	30 A	Number of Poles	Double Pole
Wire Size	#14 - #10 AWG		