Pass and Seymour

Hospital Grade Isolated Ground Tamper-Resistant 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Orange

Part No. 1597IGHGTRO

Hospital-Grade Isolated Ground Tamper-Resistant 15A Self-Test Duplex GFCI

Features & Benefits

Hospital Grade Tamper Resistant GFCI

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007048889	Country Of Origin	China
Application Sector	Residential/Commercial	Standard	cULus, UL Listed, FSUL

Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes

Additional Information

Product Environmental Profile	Yes

Technical Information

Is Tamper-Resistant	Yes	Connection	Back and side wire
Amperage	15 A	Number of Poles	Double Pole
Environmental Conditions	95% Humidity, UL 94 V2		