Pass and Seymour

Discontinued - 69W47 Turnlok Watertight Single Receptacle, Yellow

Part No. 69W47

Turnlok Watertight Single Receptacle, 30amp 125volt, NEMA Configuration L5-30, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, & corrosion.

Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007032949	Country Of Origin	United States
Standard	UL Listed, CSA Listed		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes

Technical Information

Phase	Single	Number of Wires	3
Amperage	30 A	Number of Poles	Double Pole

Wire Size	14 - 10 AWG	Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized