Ortronics

DO NOT USE Cisco® CFP-40G-LR4 Compatible 40GBase-LR4 CFP Transceiver Module with Digital Optical Monitoring

Part No. CFP-40G-LR4-LEG

This Cisco® CFP-40G-LR4 compatible CFP transceiver provides 40GBase-LR4 throughput up to 10km over single-mode fiber (SMF) at a wavelength of 1310nm using a LC connector. It is guaranteed to be 100% compatible with the equivalent Cisco® transceiver. This easy to install, hot swappable transceiver has been programmed, uniquely serialized and data-traffic and application tested to ensure that it will initialize and perform identically. Digital optical monitoring (DOM) support is also present to allow access to real-time operating parameters. All Legrand transceivers are Trade Agreements Act (TAA) compliant.

Features & Benefits

- LC ports designed for use with Single-Mode Fiber
- Supports up to 10 kilometers of cabling
- Supports Digital Optical Monitoring (DOM)
- CFP transceiver module
- 1310nm wavelength signaling

Specifications

General Info

Product Line	Legrand	Color	Silver
UPC Number	757120668831	Country Of Origin	United States
Application Sector	Commercial/Industrial	Type	Transceiver

Buy American Act Compliance

TAA Compliant	Yes

Additional Information

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes