Pass and Seymour

15A NEMA L515 Single Receptacle, Orange, Isolated Ground

Part No. IG4710

Turnlok® Single Receptacle 3-Wire 15A 125V Isolated Ground

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

One-piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Side and external screw-pressure-plate back wire capability. Accepts #14-#10 AWG.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007647105
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498		

Dimensions

Product Width US	1.437 in	Product Depth US	1.0 in
Product Height US	2.25 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes

CSA File Number	16063

Technical Information

Phase	Three	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	18 - 10 AWG		