Pass and Seymour

30A 3 Pole 4 Wire Fusible Mechanical Interlock

Part No. PS430FMIR3W



Triple pole, Four wire, Fusiable Mechanical Interlock Receptacle. 3amp, 440 vac.

Features & Benefits

Top or Bottom feed.

End user decides at installation whether top or bottom feed is appropriate.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

No closure plug kits required.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007101133	Country Of Origin	United States
Application Sector	Industrial	Standard	UL Listed

Dimensions

Product Width US	9.13 in	Product Depth US	9.53 in
Product Height US	24.5 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E31169	cULus Listed	Yes

Technical Information

Phase	Three	Number of Wires	4

Amperage	30 A	Number of Poles	3-Way
Voltage	380.0 V		