



Wiremold  
6AT Unwired Evolution™ Poke Thru Device, Surface Style Cover, Black  
Part No. 6ATC2BK



Designed for retrofit and new construction, Evolution Series 6" Recessed Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. With 3 Gangs of capacity, you will be able to configure services for the needs of your space. The low-profile metal covers are available in brushed aluminum, satin brass, satin nickel, and multiple powder-coated finishes designed to match any space. Evolution Series 6" Poke-Thru devices are the perfect fit for kiosks, meeting rooms, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture. For carpet, tile, wood and laminate concrete floor coverings.

## Features & Benefits

Preassembled unwired poke-thru device: Connect to conduits and install now, but save configuration and plate choices for later.

Step-on-it installation: Quick and easy installation without the need for additional fasteners or a second installer.

Multiple finishes: Evolution Series Poke-Thru Devices are available in multiple finishes, (BK) black, (GY) gray, (NK) nickel, (BS) brass, (BZ) bronze, (AL) aluminum, (AA) brushed aluminum, (SB) satin brass, (SN) satin nickel to seamlessly match your environment.

Open system for expanded compatibility: Accepts industry standard power, communications and A/V devices from most manufacturers including Legrand AVIP, Extron® and more.

2 hour fire rating: Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 2 hours.

UL Listed and UL fire classified to U.S. and Canadian safety standards: UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.

Recessed devices: All power, communications and A/V devices are recessed below floor level, providing maximum protection and device longevity.

Unique cover design: The cover opens a full 180 degrees with sliding doors to keep wires, connections and people safe.

Surface style cover assemblies: A surface style cover is for mounting on top of the finished floor surface. The surface cover is designed to be used for carpet, tile, wood, polished concrete, or terrazzo.

Plug load control up to 30 feet: Tested with Pass & Seymour® Wireless RF receptacles to control plug loads up to a distance of 30 feet when the cover is closed.

Meets ADA accessibility guidelines: Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.

## Specifications

### General Info

Product Line	Wiremold	Color	Black
UPC Number	786564088592	Country Of Origin	United States

Number of Knockouts	2	Application Sector	Commercial
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT, cULus Listed Nonmetallic Outlet Boxes & Fittings Classified for Fire Resistance: File R8209 Guide CEYY Meets Article 300.21 300.22[C] & 314 of NEC	Type	Poke-Thru
<b>Dimensions</b>			
Product Width US	7.25 in	Product Weight US	8.83 lb
Product Volume US	854.14 cu in	Product Depth US	16.25 in
Product Height US	7.25 in	Cubic Capacity	24.5 cu in
Core Hole Size	6 in		
<b>Listing Agencies / 3rd Party Agencies</b>			
cULus ListingNumber	E2961	cULus Listed	Yes
<b>Buy American Act Compliance</b>			
NAFTA	Yes		
<b>Additional Information</b>			
RoHS Conformant	Yes		
<b>Technical Information</b>			
Cable Entry	Knockouts & Pass Through	Number of Outlets	4