



Wiremold  
Evolution 6ATCFF Series Recessed Furniture Feed Assembly with Surface Style Cover  
Part No. 6ATCFFGY



For carpet, tile, wood and laminate concrete floor coverings. For use in 6" (152mm) diameter opening. Devices are recessed 3 1/4" (83mm) below floor surface. Die-cast aluminum cover assembly provides one (1) 3/4" trade size screw plug opening and one (1) concentric 2"-1 1/4" trade size screw plug opening and is available in the following powder coated finishes: (BK) black, (GY) gray, (NK) nickel, (BS) brass, and (BZ) bronze. INCLUDED: For Side Compartments: No Device Plates are provided. For Center Compartment: No Device Plates are provided. For Bottom Feed Compartment: One (1) 5PTHA 1/2-Gang Pass-Through Housing Assembly, One (1) 5FFHA 1 1/2-Gang Pass-Through Housing Assembly, One (1) 575CHA 1/2-Gang 3/4" Conduit Housing Assembly (also includes junction box attached to the 3/4" conduit). NOTE: UL Fire Classified for up to 2-hour rated floors.

Features & Benefits

- Aluminium cover assemblies: The Evolution Series poke-thru design includes all metal die-cast aluminium cover assemblies, with two unique spring-loaded slide egress doors. Available in surface style and flush style in standard finishes of brass, gray, black, nickel, bronze, and aluminium offering a wider range of aesthetic options.
- Added furniture feed capacity: The 6ATCFF Series Poke-Thru Device offers the largest dual service furniture feed capability on the market.
- TopGuard Protection: All Evolution Series Poke-Thru Devices like every Wiremold/Legrand Poke-Thru Device meets and exceeds UL scrub water exclusion requirements for tile, carpet, and wood covered floors.
- Meets ADA Accessibility Guidelines: Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.
- Suitable for use in air handling spaces: In accordance with Sec 300-22(C) of the National Electrical Code.
- 'Step-on-it" installation: Quick and easy installation without the need for additional fasteners or a second installer.
- UL Listed and UL Fire Classified to U.S. and Canadian safety standards. UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.
- This product meets the material restrictions of RoHS

Specifications

General Info

Product Line	Wiremold	Color	Gray
UPC Number	786564060239	Country Of Origin	United States
Number of Knockouts	2	Application Sector	Commercial
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT. cULus Listed Nonmetallic Outlet Boxes & Fittings Classified for Fire Resistance: File R8209 Guide CEYY. Meets Article 300.21 & 300.22(C) & 314 of NEC.	Type	Poke-Thru

Dimensions

Product Width US	7.75 in	Product Weight US	9.35 lb
------------------	---------	-------------------	---------

Product Volume US	976.02 cu in	Product Depth US	16.25 in
Product Height US	7.75 in	Cubic Capacity	24.5 cu in
Core Hole Size	6 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E2961	cULus Listed	Yes
Additional Information			
RoHS Conformant	Yes	Product Environmental Profile	Yes
Technical Information			
Cable Entry	Knockouts & Pass Through	Number of Outlets	0