




adore Collection

Discontinued - adore® Incandescent/Halogen Touch™ Wi-Fi Ready Master Dimmer, Magnesium
Part No. ADTH600RMHM1



Combine Wi-Fi Lighting Control with sleek touch technology and the option to dim, for truly contemporary control. The Touch Wi-Fi Ready Master Dimmer is a programmable light switch and dimmer combination that pairs with the adore Hub to create a smart Wi-Fi Lighting Control System in your home. (For 3-way, or multi-way applications, use one master device with additional remote devices.) Turn lights on/off, or adjust their brightness, with just the touch of a finger. And, create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adore® Collection, sold separately.

Features & Benefits

Installs in 25 minutes or less, fitting into an existing electrical box and wiring directly to the light. For use with incandescent/halogen bulbs.

Pair with a Touch Wi-Fi Ready Remote Dimmer to allow for 3-way control. Simply follow the provided instructions after installing to pair with the Master Dimmer.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.

Part of the adore Wi-Fi Lighting Control System, this device requires the adore Hub to operate. More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a stunning, screwless adore® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Country Of Origin	United States	Features	Indicator Lights, Smart Lighting
Switch Type	Touch	Number of Switches	1
Works With	Amazon Alexa, Google Assistant, Radio Frequency	Application Sector	Residential
Standard	cULus, FCC, UL 1472	Warranty Type	2-Year Limited Warranty

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

Additional Information

RoHS Conformant Yes

Technical Information

Actuator	Touch	Frequency Rating	900 M (RF) Hz
Number of Gangs	1	Amperage	5.5 A
Bulb Compatibility	Halogen, Incandescent	Number of Poles	3-Way, Multi-Location, Single Pole
Wattage	600 W	Mounting Type	Box
Voltage	120.0 V	Connection Type	Internal Pressure Plates
Load	Incandescent, Halogen	Environmental Conditions	0 to 80% (relative humidity, non-condensing)