




**Wiremold**  
**AMD8ATC Assembled Communications Poke-Thru Device**  
 Part No. AMD8ATCAL



All communication device accepts up to eight UTP, fiber optic, audio, or video connectors. Finish flange available in gray (GY), black (BK), ivory (VY), brushed aluminum (AL) and brass finish (BS). Aluminum and brass flanges standard with black cover. Aluminum flange also available with an aluminum colored nonmetallic cover (AA). Brass flange also available with brass colored nonmetallic cover (AB). Includes adapters to accept eight (8) Ortronics TracJack modular jacks, four (4) Ortronics Series II modular jacks, or Wiremold Open System adapters. Modular jacks sold separately. NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. AMD8 Series Poke-Thru Devices require a 4" (102mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

### Features & Benefits

All communication device accepts up to eight UTP, fiber optic, audio, or video connectors. Finish flange available in gray (GY), black (BK), ivory (VY), brushed aluminum (AL) and brass finish (BS). Aluminum and brass flanges standard with black cover. Aluminum flange also available with an aluminum colored nonmetallic cover (AA). Brass flange also available with brass colored nonmetallic cover (AB). Includes adapters to accept eight (8) Ortronics TracJack modular jacks, four (4) Ortronics Series II modular jacks, or Wiremold Open System adapters. Modular jacks sold separately. NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. AMD8 Series Poke-Thru Devices require a 4" (102mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

### Specifications

#### General Info

|                    |            |              |  |
|--------------------|------------|--------------|--|
| Product Line       | Wiremold   | UPC Number   | 786564015758   |
| Country Of Origin  | Mexico     | Construction | Assembled  |
| Application Sector | Commercial | Standard     | cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT.<br>cULus Listed Nonmetallic Outlet Boxes & Fittings Classified for Fire Resistance: File R8209 Guide CEYY. Meets Article 300.21 & 300.22(C) & 314 of NEC. |
| Type               | Poke-Thru  |              |  |

---

## Listing Agencies / 3rd Party Agencies

---

|                     |       |              |     |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | E2961 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

---

## Buy American Act Compliance

---

|       |     |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

---

## Additional Information

---

|                 |     |                               |     |
|-----------------|-----|-------------------------------|-----|
| RoHS Conformant | Yes | Product Environmental Profile | Yes |
|-----------------|-----|-------------------------------|-----|

---

## Technical Information

---

|             |  |
|-------------|--|
| Cable Entry | 1-1/4 in Trade Size Conduit Stem, 1-1/4 in |
|-------------|--|

---