



Wiremold  
Evolution™ Series 4-Gang Hinged Wall Box  
Part No. EHWB4-WH



Designed to fit into the 16" on center (406mm) opening between studs in a standard 2"x 4" (51mm x 102mm) wall. For both new work and old work applications. The box has 4-gang standard NEMA size openings and is designed to accommodate power, communications, and A/V devices. The box has been designed with a cable pass-through capability, allowing multiple service access points to be daisy chained together, eliminating the need for multiple conduit runs. Box includes temporary cover. Finished cover assembly (EHWB4C) sold separately.

## Features & Benefits

Available in both 4- and 8-gang versions to provide maximum flexibility.

Cover opens a full 180° and can be painted to blend with room decor. Includes integrated handle, lock and key set for security, and flush egress door for cabling.

Accepts Legrand AVIP devices, plus A/V devices from leading manufacturers.

Accepts trade size service feeds from 3/4" up to 2". Knockout plates are removable and interchangeable, providing multiple options.

Both boxes (4- and 8-gang) fit are designed to fit in 16" opening between studs in standard 2" x 4" [51mm x 102mm] wall.

Finished interior eliminates industrial look for upscale installations, while increasing visibility, making it easier to locate.

Built-in tunnel & feed through capability allows service feeds to be fed through the box, reducing the number of feeds required to reduce installation time.

Designed to accept standard 1- to 4-gang device plates. No proprietary plates simplifies ordering and installation.

3 5/8" [92mm] of space behind device plates provides the extra depth needed for wiring larger A/V devices.

Can be installed in new work and old work installations. New hardware not necessary.

UL Listed to U.S. and Canadian safety standards.

## Specifications

### General Info

|                    |               |              |   |
|--------------------|---------------|--------------|---|
| Product Line       | Wiremold      | UPC Number   | 786564085577  |
| Country Of Origin  | United States | Construction | Assembled   |
| Application Sector | Commercial    | Standard     | cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC. |

|                                       |           |                   |            |
|---------------------------------------|-----------|-------------------|------------|
| Type                                  | Floor Box |                   |            |
| Dimensions                            |           |                   |            |
| Product Width US                      | 7.98 in   | Product Depth US  | 3.98 in    |
| Product Length US                     | 10.98 in  | Cubic Capacity    | 56.9 cu in |
| Listing Agencies / 3rd Party Agencies |           |                   |            |
| cULus ListingNumber                   | E2961     | cULus Listed      | Yes        |
| Buy American Act Compliance           |           |                   |            |
| NAFTA                                 | Yes       |                   |            |
| Additional Information                |           |                   |            |
| RoHS Conformant                       | Yes       |                   |            |
| Technical Information                 |           |                   |            |
| Cable Entry                           | Knockouts | Number of Outlets | 4          |