




Wiremold
RC9AMDTC Communications Assembled Poke-Thru Device
Part No. RC9AMDTCAB



All communication device accepts up to four UTP connectors. Flange available in painted gray (GY), black (BK), ivory (VY), and brushed metal finishes in aluminum (AL) and brass (BS). Aluminum and brass flanges shipped with black cover. Brass flange also available with brass colored cover assembly (AB). Aluminum flange also available with aluminum colored cover assembly (AA). Unit includes two (2) Ortronics TracJack adapters, two (2) Ortronics Series II adapters, and two (2) Wiremold Open System adapters. Modular jacks sold separately. NOTE: Includes two Cat 6 TechChoice discrete keystone connectors, two Ortronics TracJack adapters, and two Wiremold Open System adapters. RC9AMD Series Poke-Thru Devices require a 3 1/16" (78mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

Features & Benefits

All communication device accepts up to four UTP connectors. Flange available in painted gray (GY), black (BK), ivory (VY), and brushed metal finishes in aluminum (AL) and brass (BS). Aluminum and brass flanges shipped with black cover. Brass flange also available with brass colored cover assembly (AB). Aluminum flange also available with aluminum colored cover assembly (AA). Unit includes two (2) Ortronics TracJack adapters, two (2) Ortronics Series II adapters, and two (2) Wiremold Open System adapters. Modular jacks sold separately. NOTE: Includes two Cat 6 TechChoice discrete keystone connectors, two Ortronics TracJack adapters, and two Wiremold Open System adapters. RC9AMD Series Poke-Thru Devices require a 3 1/16" (78mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

Specifications

General Info

| | | | |
|---------------------|--|--------------------|--------------|
| Product Line | Wiremold | UPC Number | 786564006695 |
| Country Of Origin | Mexico | Construction | Assembled |
| Number of Knockouts | 1 | Application Sector | Commercial |
| Standard | cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT, cULus Listed Nonmetallic Outlet Boxes & Fittings Classified for Fire Resistance: File R8209 Guide CEYY Meets Article 300.21 300.22[C] &314 of NEC | Type | Poke-Thru |

Dimensions

| | | | |
|------------------|--------|-------------------|---------|
| Product Width US | 7.0 in | Product Height US | 10.0 in |
|------------------|--------|-------------------|---------|

Listing Agencies / 3rd Party Agencies

cULus ListingNumber E2961

cULus Listed

Yes

Buy American Act Compliance

NAFTA

Yes

Additional Information

RoHS Conformant

Yes

Technical Information

Cable Entry

CONDUIT
