Pass and Seymour

SteriGuard™ Antimicrobial Straight Blade Plug 15A, 125V, Yellow

Part No. 14W47AM



SteriGuard Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure

Features & Benefits

- UL and CSA Listed
- Patent Pending
- Anti-microbial Additive Resistant to Scuffing and Cleaning
- Staphylococcus (Staph), MRSA: - Log Reduction greater than 4.3, reduces surface bacteria by greater than 99.97%
- RoHS Compliant (Non-Halogenated)
- Resistant to High Pressure Hose-down applications
- Keyed Body and Cover for Alignment
- Steriguard: Anti-microbial Wiring Devices are ideal for a wide range of applications including food and beverage preparation, procession, & packaging: agriculture, pharmaceutical, and health care.
- NSF (National Sanitation Foundation) Certified
- Anti-microbial Additives Embedded in polymer and inhibits Growth of Bacteria, Molds, Mildews and Fungi
- Escherichia (E.Coli): - Log reduction greater than 4.8, reduced surface bacteria by greater than 99.99%
- Salmonella : Log Reduction Greater Than 3.6, reduces surface bacteria by Greater Than 99.97%
- Independently tested and Certified to JIS Z2801 standards
- Tongue & Groove Environmental Sealing
- NEMA Type 4, 4x, 6, 6P and IP67 Protection

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Application Sector	Commercial

Standard	CSA Listed, FSUL, UL Listed

Dimensions

Product Width US	1.85 in	Product Depth US	2.62 in

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes

Technical Information

Phase	Single	Connection	Cable
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	18 - 12 AWG
Voltage	125 V	Environmental Conditions	Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized