



Legrand
SteriGuard™ Straight Blade Plug 20A, 125V
Part No. 14W33AM

"SteriGuard Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure"



Features & Benefits

UL and CSA Listed	NSF (National Sanitation Foundation) Certified
Patent Pending	Anti-microbial Additives Embedded in polymer and inhibits Growth of Bacteria, Molds, Mildews and Fungi
Anti-microbial Additive Resistant to Scuffing and Cleaning	Escherichia [E.Coli]: - Log reduction > 4.8, reduced surface bacteria by > 99.99%
Staphylococcus (Staph), MRSA: - Log Reduction > 4.3, reduces surface bacteria by > 99.97%	Salmonella : Log Reduction > 3.6, reduces surface bacteria by > 99.97%
RoHS Compliant (Non-Halogenated)	Independently tested and Certified to JIS Z2801 standards
Resistant to High Pressure Hose-down applications	Tongue & Groove Environmental Sealing
Keyed Body and Cover for Alignment	NEMA Type 4, 4x, 6, 6P and IP67 Protection
Steriguard: Anti-microbial Wiring Devices are ideal for a wide range of applications including food and beverage preparation, procession, & packaging: agriculture, pharmaceutical, and health care.	

Specifications

General Info

Color	Yellow
UPC Number	785007056990
Country Of Origin	United States
Product Line	Pass & Seymour
Application Sector	Commercial
Standard	CSA Listed, FSUL, UL Listed

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

Technical Information

Number of Poles Double Pole

Voltage 125 V

Connection Cable

Phase Single

Wire Size 18AWG - 12AWG

Number of Wires 3

Environmental Conditions Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized
