




Pass and Seymour  
 SteriGuard™ Antimicrobial Straight Blade Plug 20A, 250V, Yellow  
 Part No. 14W48AM



SteriGuard Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure

## Features & Benefits

|                                                                                                                                                                                                      |                                                                                                         |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------|
| UL and CSA Listed                                                                                                                                                                                    | NSF (National Sanitation Foundation) Certified                                                          |
| Patent Pending                                                                                                                                                                                       | Anti-microbial Additives Embedded in polymer and inhibits Growth of Bacteria, Molds, Mildews and Fungi  |
| Anti-microbial Additive Resistant to Scuffing and Cleaning                                                                                                                                           | Escherichia (E.Coli): - Log reduction greater than 4.8, reduced surface bacteria by greater than 99.99% |
| Staphylococcus (Staph), MRSA: - Log Reduction greater than 4.3, reduces surface bacteria by greater than 99.97%                                                                                      | Salmonella : Log Reduction Greater Than 3.6, reduces surface bacteria by Greater Than 99.97%            |
| RoHS Compliant (Non-Halogenated)                                                                                                                                                                     | Independently tested and Certified to JIS Z2801 standards                                               |
| Resistant to High Pressure Hose-down applications                                                                                                                                                    | Tongue & Groove Environmental Sealing                                                                   |
| Keyed Body and Cover for Alignment                                                                                                                                                                   | NEMA Type 4, 4x, 6, 6P and IP67 Protection                                                              |
| Steriguard: Anti-microbial Wiring Devices are ideal for a wide range of applications including food and beverage preparation, procession, & packaging: agriculture, pharmaceutical, and health care. |                                                                                                         |

## Specifications

### General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | Yellow     |
| Country Of Origin | United States  | Application Sector | Commercial |

---

|          |                             |
|----------|-----------------------------|
| Standard | CSA Listed, FSUL, UL Listed |
|----------|-----------------------------|

---

## Dimensions

---

|                  |         |                  |         |
|------------------|---------|------------------|---------|
| Product Width US | 1.85 in | Product Depth US | 2.62 in |
|------------------|---------|------------------|---------|

---

## Listing Agencies / 3rd Party Agencies

---

|            |     |
|------------|-----|
| CSA Listed | Yes |
|------------|-----|

---

## Technical Information

---

|       |        |            |       |
|-------|--------|------------|-------|
| Phase | Single | Connection | Cable |
|-------|--------|------------|-------|

---

|                 |   |          |      |
|-----------------|---|----------|------|
| Number of Wires | 3 | Amperage | 20 A |
|-----------------|---|----------|------|

---

|                 |             |           |             |
|-----------------|-------------|-----------|-------------|
| Number of Poles | Double Pole | Wire Size | 18 - 12 AWG |
|-----------------|-------------|-----------|-------------|

---

|         |         |                          |                                                                                                                                                                                                                                                                                                                 |
|---------|---------|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Voltage | 250.0 V | Environmental Conditions | Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized |
|---------|---------|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

---